

# OPTIMA® SENSOR FAUCET EAF-100-HLT-CP-1.5GPM-AER-IQ-FCT

(General Model Name: EAF100-LT CP ELECT FCT (IQ))

#### **CODE NUMBER**

3335012

## **DESCRIPTION**

Bluetooth Adapter, Hardwired Less Transformer Power Supply, Mixer Not Included, Polished Chrome Finish, 1.5 gpm, Aerated Spray, Infrared Sensor, Optima® Hardwired-Powered Deck-Mounted Mid Body Faucet.

## **DETAILS**

• Flow Rate: 1.5 gpm (5.7 Lpm) (1.5GPM)

Spray Type: Aerated (AER)Sensor Type: InfraredMounting Type: Single Hole

• Power Supply: Hardwired Less Transformer (HLT)

• Temperature Mixer: Mixer Not Included

• Finish: Polished Chrome (CP)

Factory Default Timeout: 30 secondsFactory Default Gallons per Cycle: 0.75

#### **FEATURES**

Commercial Grade, ADA Compliant, Electronic, Sensor-Activated, Cast Brass Hand Washing Faucet with the following features:

- Double Infrared Sensors with Automatic Setup and Indicator Light
- Automatic Self-adapting Sensor Technology
- Magnetic Solenoid Valve
- Water Supply Connection with Flexible High-pressure Hose and Strainer
- 6 Volt DC Plug-in Adapter (must be ordered separately for Less transformer (-LT) faucets)
- Daisy Chain Electrical Splitter Cable included with Less transformer (-LT) faucets
- Appropriate Mounting Hardware included
- Optional 24 Hour Sentinel Activation
- IQ-Click feature permits activation of continuous run and temporary off modes
- Includes EAF44 Power Splitter

## **ELECTRICAL SPECIFICATIONS**

Sensor Range: 4"-5" (102-127mm)
Timeout Adjustment Settings: 30s

## **VIDEOS**




Sloan Connect App®

## **DOWNLOADS**

- EAF 100/150 Installation Instructions
- EAF 100/150 (SP) Installation Instructions
- Optima Plus EAF 100 Repair and Maintenance Guide
- Faucet Spray Heads Repair and Maintenance Guide
- Trim Plate Guide





## **COMPLIANCES & CERTIFICATIONS**





























(ADA Compliant, ASME A112.18.1 Compliant, CEC Compliant, cUPC Certified, cUPC Low Lead Compliant, EPD, HPD, IAPMO, Proposition 65, TAS, UPC Certified, UPC Low Lead Compliant, WaterSense Listed, WELL Building Standard)

### **NOTES**

All information contained within this document subject to change without notice.

Looking for other variations of the EAF-100 product? View the general spec sheet with all options.

Find a matching soap dispenser for this faucet. Find a compatible sink for this faucet.

### WARRANTY

View Warranty Information



# OPTIMA® SENSOR FAUCET EAF-100-HLT-CP-1.5GPM-AER-IQ-FCT

(General Model Name: EAF100-LT CP ELECT FCT (IQ))


• Additional Downloads




## OPTIMA® SENSOR FAUCET EAF-100-HLT-CP-1.5GPM-AER-IQ-FCT

(General Model Name: EAF100-LT CP ELECT FCT (IQ))

### **ROUGH-IN**





When the EAF faucet is installed on a sink that has three (3) hole punchings, a Trim Plate should be used. Trim Plates must be specified and ordered separately:

SFP-11

Trim Plate for 4" (102 mm) Centerset Sink

SFP-22

Trim Plate for 8" (204 mm) Centerset Sink

Phone: 800.982.5839 • Fax: 800.447.8329 • sloan.com