

# OPTIMA® SENSOR FAUCET EAF-750-BAT-ISM-CP-1.0GPM-LAM-IQ-FCT

(General Model Name: EAF750-ISM CP BATT FCT W/ MIX 1.0GPM)

#### **CODE NUMBER**

3335125

#### **DESCRIPTION**

Battery Power Supply, Integrated Side Mixer, Polished Chrome Finish, 1.0 gpm, Laminar Spray, Infrared Sensor, Optima® Battery-Powered Deck-Mounted Gooseneck Body Faucet.

#### **DETAILS**

• Flow Rate: 1.0 gpm (3.8 Lpm) (1.0GPM)

Spray Type: Laminar (LAM)
Sensor Type: Infrared
Mounting Type: Single Hole
Power Supply: Battery (BAT)

• Temperature Mixer: Integrated Side Mixer (ISM)

• Finish: Polished Chrome (CP)

Factory Default Timeout: 30 secondsFactory Default Gallons per Cycle: 0.5

### **FEATURES**

Commercial Grade, ADA Compliant, Electronic, Sensor-Activated, Cast Brass Gooseneck Hand Washing Faucet with the following features:

- 12/24 Hour Hygienic Rinse Line Purge Function Field Settable
- Unitary Spout Housing Assembly for Easy Cleaning
- Modular One-piece Construction with all Concealed Components above deck
- Double Infrared Sensors with Automatic Setting Feature and Microprocessor
- Low Battery Indicator
- Bi-stable Magnetic Solenoid Valve
- Water Supply Connection with Flexible High-pressure Hose and Strainer
- 7 volt Lithium CR P2 Commercial Battery included
- Appropriate Mounting Hardware included
- IQ-Click feature permits activation of continuous run and temporary off modes
- Installation Similar to Conventional Single Lever Faucet

## **ELECTRICAL SPECIFICATIONS**


Battery Life: 3 years 8,000 cycles/month
 Optional power harvesting significantly extends service life

Sensor Range: 4"-5" (102-127mm)
Timeout Adjustment Settings: 30s

## **DOWNLOADS**

- EAF 700/750 Installation Instructions
- Faucet Spray Heads Repair and Maintenance Guide
- Optima Plus EAF 750 Repair and Maintenance Guide
- Trim Plate Guide
- Additional Downloads





## **COMPLIANCES & CERTIFICATIONS**



(ADA Compliant, ASME A112.18.1 Compliant, CEC Compliant, cUPC Certified, cUPC Low Lead Compliant, EPD, HPD, IAPMO, Proposition 65, TAS, UPC Certified, UPC Low Lead Compliant, WaterSense Listed, WELL Building Standard)

## NOTES

All information contained within this document subject to change without notice.

Looking for other variations of the EAF-750 product? View the general spec sheet with all options.

Find a matching soap dispenser for this faucet. Find a compatible sink for this faucet.



# OPTIMA® SENSOR FAUCET EAF-750-BAT-ISM-CP-1.0GPM-LAM-IQ-FCT

(General Model Name: EAF750-ISM CP BATT FCT W/ MIX 1.0GPM)

### WARRANTY


View Warranty Information





#### **ROUGH-IN**

EAF-750-ISM Faucets with Hot and Cold Water Supply



When the EAF faucet is installed on a sink that has three (3) hole punchings, a Trim Plate should be used. *Trim Plates must be specified and ordered separately:* 

## SFP-11

Trim Plate for 4" (102 mm) Centerset Sink

## SFP-22

Trim Plate for 8" (204 mm) Centerset Sink